

# Boiled Glass - Unique Glass Colors Style



This was done using four pieces of float glass (or more, or less). You can really use any glass you like as long as it is compatible.

All NT Colors plus Lite Red, Orange and Brite Yellow were used on the sample.

Bottom piece - only color on the top side. All the other subsequent pieces have color on both sides, can be solid or a variety of colors.

When all the glass has color and it has dried - on the bottom piece of glass - place UGC Bubble Powder in little heaps. Stack the pieces of glass on top of one another and place in kiln, making sure that there is a dam placed around the glass. For float glass, take it up to 1700F, hold for 10-20 min and then bring it down. You open the kiln and either go OMG, I love it or Hmmm, that was a waste of color.....Dr. SJ (Saulius Jankauskas)

300 Ryder Lane Unit 1000, Casselberry, FL 32707  
407.261.0900 Fax: 407.331.0900  
Uniqueglasscolors.com info@uniqueglasscolors.com